



# Real Lady

Crafts your muse

## Real Lady ULW White Paper 2026

**A Lighter Way to Experience Realism**

**Less Weight. More Comfort. Same Real Lady Experience.**

A brand-formatted overview of Real Lady ULW, including the product logic, production principles, verified Real Lady production data, selected model results, testing direction, and important usage notes.

---

## EXECUTIVE SUMMARY

## Realism Should Feel Easier to Own

Real Lady has always been associated with graceful proportions, full curves, and a refined visual presence. ULW was developed to reduce the physical burden of ownership while preserving the look, touch, and confidence users expect from a Real Lady body.

- 
- Reduces overall weight through an optimized lightweight internal structure.
  - Supports easier lifting, repositioning, dressing, cleaning, and storage.
  - Aims to preserve realistic body character and familiar silicone response.
  - Builds around four communication pillars: Up to 35% Lighter\*, Realistic Look. Familiar Touch., Reliable Support. Lasting Durability., and Easier Everyday Use.

## PRODUCT LOGIC

## Why ULW Matters for Real Lady

For many users, the appeal of a fuller body is easy to understand. The challenge comes later—when that same body needs to be moved, positioned, dressed, cleaned, or stored. ULW addresses that ownership challenge directly.

- 
- Makes full-size handling more approachable in everyday life.
  - Helps reduce strain during repeated lifting and repositioning.
  - Supports a better overall experience for dressing, care, photography, and display.
  - Allows users to stay closer to the body type they really want instead of choosing around weight alone.

## CORE VALUE

## Lighter, Without Losing What Matters

ULW is not intended to change what makes a Real Lady body desirable. The goal is to reduce unnecessary weight while keeping the visible and tactile experience as familiar as possible.

- 
- Up to 35% Lighter\* — approved brand communication for selected ULW models and configurations.
  - Realistic Look. Familiar Touch. — designed to preserve natural curves, visual fullness, and the familiar silicone response.
  - Reliable Support. Lasting Durability. — aimed at stable support and dependable repeated handling.
  - Easier Everyday Use — a more manageable experience across lifting, positioning, dressing, cleaning, and storage.

## PRODUCTION PRINCIPLE

## Precision Without Unnecessary Compromise

ULW is achieved through a more controlled manufacturing approach rather than a simple reduction in material. The process is intended to reduce weight while supporting consistency, touch, and structural confidence.

- Ultra-slow pouring at approximately 3–5 grams per second with fast-curing control.
- Five independent pouring zones with customized parameters for different areas of the body.
- Real-time supervision by two technicians throughout the process.
- Three industrial endoscopes used to help observe internal voids, air pockets, and potential weak points.
- Up to 1–2 hours of focused production and monitoring for a single ULW body.

**ULW is not about doing less. It is about doing more—with greater control and care.**

VERIFIED REAL LADY DATA

## Weight Reduction Data

The following section uses Real Lady-only actual production records. These results do not include Irontech or LN-prefixed data. Based on the current production sheet, Real Lady ULW has 15 computable records across 4 verified body models, plus 1 RL170 ULW record that is not yet fully computable because the standard weight is still missing.

|                    |                      |                      |                          |                            |
|--------------------|----------------------|----------------------|--------------------------|----------------------------|
| <b>15</b>          | <b>4</b>             | <b>6.1 kg</b>        | <b>16.5%</b>             | <b>20.7%</b>               |
| Computable Records | Verified Body Models | Average Weight Saved | Average Weight Reduction | Highest Verified Reduction |

### Selected Verified Results

|                                                                                                                                    |                                                                                                                                      |                                                                                                                                      |                                                                                                                                    |
|------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| <b>RL159</b><br><b>20.7% Lighter</b><br><b>38.2 kg → 30.3 kg</b><br><small>Standard      ULW</small><br><b>7.9 kg Weight Saved</b> | <b>RL150</b><br><b>19.7% Lighter</b><br><b>32.75 kg → 26.3 kg</b><br><small>Standard      ULW</small><br><b>6.45 kg Weight Saved</b> | <b>RL168-3</b><br><b>16.4% Lighter</b><br><b>44.0 kg → 36.8 kg</b><br><small>Standard      ULW</small><br><b>7.2 kg Weight Saved</b> | <b>RL168</b><br><b>13.6% Lighter</b><br><b>44.0 kg → 38.0 kg</b><br><small>Standard      ULW</small><br><b>6.0 kg Weight Saved</b> |
|------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|

RL170 currently has a recorded ULW weight of 36 kg in the production log, but the corresponding standard weight is missing. As a result, its weight-saving amount and reduction percentage should not be published as verified figures until the standard reference weight is confirmed.

### TESTING DIRECTION

## Tested for Everyday Use

A lighter body must still feel trustworthy. ULW evaluation therefore considers not only weight change, but also everyday-use stability, touch, and structural behavior.

- Touch and softness evaluation.
- Waist twisting, arm lifting, and torso folding.
- Knee articulation, sitting, kneeling, and full-split positions.
- Long-term deformation resistance and structural stability observation.

- Extended position holding, including sitting and kneeling for 12 consecutive hours and continuous durability observation over 9 days.

*Observed test outcomes include no tearing, no abnormal bulging, and no structural failures in the reported internal evaluations.*

#### USER EXPERIENCE

## Where the Difference Is Felt Most

The value of ULW becomes obvious in routine ownership. The most important change is not how the body looks. It is how the body feels to manage over time.

- 
- Lifting the body onto a bed or sofa.
  - Repositioning it during everyday handling.
  - Changing outfits and cleaning with less physical effort.
  - Preparing the body for photography or display.
  - Putting the body away after use or moving it into storage.

#### CONCLUSION

## The Same Real Lady Experience, Made Easier

ULW is a product-direction upgrade aimed at comfort, practicality, and a more manageable ownership journey. It is not about taking away what makes a Real Lady body appealing. It is about making that experience easier to live with.

---

## Less Weight. More Comfort. Same Real Lady Experience.

#### DISCLAIMER

## Important Notes on Data Usage

This white paper is based on the currently available Real Lady production records and approved brand communication language.

- 
- \*Up to 35% lighter applies to selected ULW models and configurations as an approved brand communication claim.
  - Within the current Real Lady-only verified production records summarized here, the highest confirmed reduction is approximately 20.7%.
  - RL170 currently has an incomplete real-world record because the standard comparison weight is missing. Its verified reduction percentage should not be claimed until that reference weight is confirmed.
  - Actual product weight and reduction percentage vary according to body size, internal structure, functional configuration, softness options, and customization.